


DATASHEET

OCU-490-20 UE435-XG



High Power Deep blue LED with Glass Lens

Features:

- Footprint: 6046 (2318)
- Size: 6.0(L) x 4.6(W) x 4.3(H) mm
- Circuit substrate: Ceramics
- ROHS and REACH compliant
- Lead-free solderable
- All devices sorted into intensity classes
- Taped in 16 mm blister tape
- Taping: face-up (T)

Applications:

- Sensing
- Medical
- Security
- Curing

This 435 nm high power deep blue LED is designed for medical light therapy applications where a small, high optical density spot is required. A glass lens with narrow view angle enables exact delivery of the light.

Typical Electro-Optical Characteristics

Measurement conditions

 $T_{\text{ambient}} = 23\text{ }^{\circ}\text{C}$; $t_{\text{test}} \leq 60\text{ ms}$

Parameter	Symbol	Condition	Min	Typ	Max	Unit
Emitting Color	Deep blue					
Forward Voltage	V_f	$I_f = 350\text{ mA}$		3.2	3.6	V
		$I_f = 1000\text{ mA}$		3.5		
Peak Wavelength	λ_p	$I_f = 350\text{ mA}$	430	435	440	nm
		$I_f = 1000\text{ mA}$		433		
FWHM	$\Delta\lambda$	$I_f = 350\text{ mA}$		20		nm
		$I_f = 1000\text{ mA}$		22		
Radiant Intensity ⁽¹⁾	I_e	$I_f = 350\text{ mA}$	710	1400		mW/sr
		$I_f = 1000\text{ mA}$		3200		
View Angle	θ	$I_f = 350\text{ mA}$		20		deg.
Reverse Current ⁽²⁾	I_R	$V_R = 5\text{ V}$			—	μA

(1) Measured according to the CIE 127, Condition B

(2) LED should never be operated with reverse bias


Maximum Ratings

Parameter	Symbol	Min	Max	Unit
Forward Current	$I_{f, \text{max}}$		1000	mA
Forward Current, pulsed	$I_{f, \text{pulse}}$	$t_p \leq 100\mu\text{s}$, $\tau=1:10$	1200	mA
Reverse Voltage	V_R		—	V
Thermal Resistance Junction – Solder point	$R_{th_{JS}}$		5	K/W
Operating Temperature	T_{op}	-40	+85	$^{\circ}\text{C}$
Storage Temperature	T_{st}	-40	+85	$^{\circ}\text{C}$


Electrostatic discharge classification (MIL-STD-883): Class 1




Typical Performance




Forward Current vs. Forward Voltage




Relative Intensity vs. Forward Current



Optical Spectrum




Wavelength Shift vs. Forward Current



Maximum Ratings ⁽¹⁾

(1) Assuming connection to an infinite heatsink if not stated otherwise



Radiation Pattern

Outline Drawing


Unless otherwise specified, all drawing units are in mm
Tolerances are: ISO 2768-m



Marking at the Anode side.

Recommended soldering pad

Unless otherwise specified, all drawing units are in mm



Soldering Profile



IR reflow
soldering
profile for lead
free soldering




IR reflow
soldering profile
for solder
containing lead

Manual Soldering:

Not applicable for manual soldering.

Tape And Reel Packaging



D	Parts/reel
7"	400

Packaging

The reel is sealed in a special plastic bag with integrated ESD protection including a silica dry-pack. Shelf life for sealed bag: 12 months on max. 30 °C and 60% Rh. Floor life: 12 months under max. 30 °C and 60% Rh in a dust free environment. Other bags (i.e. MBB, HIC, Vacuum pack, etc.) available on request.

LED Intensity Groups [mW/sr]

All SMD-LED devices are 100% measured and sorted into intensity groups with an accuracy of $\pm 11\%$.
Intensity group is measured according to CIE 127.

General information – not this specific device.

C:	0.28	-	0.45
D:	0.45	-	0.71
E:	0.71	-	1.12
F:	1.12	-	1.80
G:	1.80	-	2.80
H:	2.80	-	4.50
J:	4.50	-	7.10
K:	7.10	-	11.20
L:	11.20	-	18.00
M:	18	-	28
N:	28	-	45
P:	45	-	71
Q:	71	-	112
R:	112	-	180
S:	180	-	280
T:	280	-	450
U:	450	-	710
V:	710	-	1120
AW:	1120	-	1800
BW:	1800	-	2800
CW:	2800	-	4500
DW:	4500	-	7100
EW:	7100	-	11 200
FW:	11 200	-	18 000
GW:	18 000	-	28 000
HW:	28 000	-	45 000
JW:	45 000	-	71 000
KW:	71 000	-	112 000
LW:	112 000	-	180 000
MW:	180 000	-	280 000

Special service: EPIGAP OSA offers Radiant intensity selection (binning) in sub selections.

Color selection in 3 sub-selections possible (each subgroup on a separate reel).

Information on available sub-groups can be accessed through this link:

https://www.epigap-osa.com/datasheet/SMD_LED_Intensity_Groups_And_Subgroups_EPIGAP_OSA.pdf

Warnings (UV light)

- While in operation UV LEDs emit intense but mainly invisible ultraviolet radiation, which may be harmful to eyes, even for brief periods.
- Do not look directly into the UV LED during operation.
- Be sure that you and everyone in the vicinity wear safety goggles that provide suitable UV protection when operating a UV LED.
- Please follow all standard procedures for storing, handling, cleaning, mounting, soldering, disposing, or otherwise handling LED dies or packaged LEDs, including static electricity protection.
- The user has the responsibility to inform, train and instruct, customers and employees of the dangers to eye safety.
- UV LEDs are ESD sensitive (Class1). Handling and use of UV LEDs must be compatible with the ESD sensitivity rating.

Notice

The information describes the type of component and shall not consider as assured characteristics. Terms of delivery and rights to change reserved. The data sheet may change without prior notification; the only valid issue and current revision can be on our website. Due to technical requirements, components may contain dangerous substances.

It is the responsibility of the customer to evaluate and ensure that the use of the products in their specific applications complies with relevant safety standards and regulations. Customers must assess the exposure conditions within their systems and ensure that appropriate measures are taken to prevent exceeding the permissible exposure limits outlined in IEC 62471. EPIGAP OSA Photonics GmbH does not assume liability for any non-compliance arising from the integration or usage of LEDs in customer systems.

Parameters can vary in different applications. The customer must validate all operating parameters for each application. EPIGAP OSA Photonics GmbH does not have the responsibility for the reliability and the degradation behavior of products made with EPIGAP OSA Photonics GmbH diodes as they depend not only on the product itself but also on the operation, manufacturing or design of the final products. The customer is responsible for ensuring the long-term stability of the product according to their requirements. If components are used in toys or, life support systems, EPIGAP OSA Photonics GmbH must expressly authorize the use of the components prior to incorporating them into the customer's systems! Packaging: EPIGAP OSA Photonics GmbH uses recyclable packages.

EPIGAP OSA Photonics GmbH

www.epigap-osa.de

Köpenicker Str.325
12555 Berlin Germany
Tel. +49 (0)30 6576 3764
sales@epigap-osa.de

