


M1650D2



Description

Thorlabs' M1650D2 LED on a Metal-Core Printed Circuit Board (MCPCB) is designed to provide high-power output in a compact package and has a nominal wavelength of 1650 nm. The minimum emitted power is 13 mW, and the typical emitted power is 16 mW. For more specifications, please see the table below.

Thermal Management

Please note that operation of this LED requires mounting of the LED to an adequate heat sink. For proper thermal management, fix the MCPCB to a heat sink using two screws and use a thermal compound to provide good thermal contact between the MCPCB and the heat sink.

Specifications

Specifications	
Color	IR
Nominal Wavelength	1650 nm
Test Current for Typical LED Power	600 mA
Maximum Current (CW)	600 mA
Bandwidth (FWHM)	120 nm
Viewing Angle (Full Angle at Half Max)	20°
Electrical Power	660 mW
Typical Lifetime	>10 000 h
Chip Size	1 mm x 1 mm
MCPCB Thickness	2.4 mm
Operating Temperature (Non-Condensing)	0 to 40 °C
Storage Temperature	-40 to 70 °C
Risk Group ^a	RG0 - Exempt Group

a. According to the standard IEC 62471:2006, Photobiological Safety of Lamps and Lamp Systems

M1650D2				
	Symbol	Min	Typical	Max
Peak Wavelength ^a	λ_p	1600 nm	1650 nm	1700 nm
LED Power Output ^b	P_{out}	13 mW	16 mW	-
Forward Voltage	V_F	-	1.1 V	-
Maximum Irradiance ^c	E_e	-	1.2 $\mu W/mm^2$	-


a. When Driven with a Current of 500 mA

b. When Driven with Test Current


c. Measured at a Distance of 200 mm

Power Supply


M1650L4 Spectrum




Typical Peak Wavelength vs. Temperature





Typical Spatial Radiation Distribution



Typical Forward Current



Drawings



Power Supply

We recommend using Thorlabs' DC2200 or LEDD1B LED current drivers (for control of a single LED). Alternatively, the DC4100 or DC4104 current driver can be used with the DC4100-HUB, which allows simultaneous control of up to 4 individual LEDs.

If you decide to use your own DC source, please make sure that the operating current does not exceed the maximum allowed value, sufficient forward voltage is supplied, and that the correct connection is made to Pins 1 and 2.

Maintenance and Service

This LED is not water resistant and must be protected from adverse weather conditions. To avoid damage, do not expose it to spray, liquids, or solvents. The LED does not contain any parts serviceable by the user and does not require regular user maintenance. If a malfunction occurs, contact Thorlabs for return instructions.

Warnings and Safety

Inappropriate use of any LED product may result in permanent eye damage. To prevent injury, use this product in accordance with the International Standard "Photobiological Safety of Lamps & Lamp Systems" IEC 62471. This product falls under Risk Group RG0 - Exempt Group in accordance to the standard IEC 62471:2006.

If using this LED in a microscope application as a replacement for mercury vapor lamp, the same precautions should be taken.

Please note that this product is not suitable for household room illumination.

This LED must not be operated in explosive environments and should only be used with shielded connection cables.

All statements regarding safety of operation and technical data only apply when the unit is operated correctly according to its specifications. The safety of any system incorporating the equipment is the responsibility of the assembler of the system.

CAUTION!

TO ENSURE PROPER HEAT MANAGEMENT,
MOUNT THE METAL CORE PRINTED CIRCUIT
BOARD (MCPCB) TO AN ADEQUATE HEAT SINK

